

Electrical Nonmetallic Tubing Dimensions

Table 1: ENT Dimensions

Metric designator (trade size)		Outside diameter (OD)				Inside diameter (ID)			
		Minimum		Maximum		Minimum		Maximum	
		mm	(In)	mm	(In)	mm	(In)	mm	(In)
16	(1/2)	21.13	(0.832)	21.54	(0.848)	14.58	(0.574)	16.00	(0.630)
21	(3/4)	26.42	(1.040)	26.92	(1.060)	19.66	(0.774)	21.18	(0.834)
27	(1)	33.15	(1.305)	33.66	(1.325)	25.37	(0.999)	26.90	(1.059)
35	(1-1/4)	41.86	(1.648)	42.47	(1.672)	33.73	(1.328)	35.36	(1.392)
41	(1-1/2)	47.96	(1.888)	48.56	(1.912)	39.57	(1.558)	41.20	(1.622)
53	(2)	60.02	(2.363)	60.63	(2.387)	51.18	(2.015)	52.81	(2.079)

Figure 1: ENT Geometry

