



# 01233

75A19 IF/RS/VS 120-130V (PK X 12)



**Application:** Rough & Vibration Service, General Lighting

**Base:** Medium (E26)

**Coating:** PFA

**Diameter:** 2.38 IN

**Finish:** Inside Frost

**Lamp Type:** Incandescent

**Mean Design Lumens:** 712

**Package (LxWxH):** 11.75 IN x 9.00 IN x 5.25 IN

**Pack By:** 12

**Special Features:** Shatter-Resistant

**UPC:** 726585012336

**Wattage:** 75.0 W

**Average Life Hours:** 1700

**Bulb:** A19

**CRI:** 100

**Filament Type:** RC-9

**Initial Lumens:** 712

**Length:** 3.94 IN

**Operating Position:** Universal

**Package Weight:** 1.60 L

**Shape:** A19

**Type:** Incandescent

**Voltage:** 120-130 V

ULEPH,ROHS,NSF Splash Zone



# 01233

75A19 IF/RS/VS 120-130V (PK X 12)



**Application:** Rough & Vibration Service, General Lighting

**Base:** Medium (E26)

**Coating:** PFA

**Diameter:** 2.38 IN

**Finish:** Inside Frost

**Lamp Type:** Incandescent

**Mean Design Lumens:** 712

**Package (LxWxH):** 11.75 IN x 9.00 IN x 5.25 IN

**Pack By:** 12

**Special Features:** Shatter-Resistant

**UPC:** 726585012336

**Wattage:** 75.0 W

**Average Life Hours:** 1700

**Bulb:** A19

**CRI:** 100

**Filament Type:** RC-9

**Initial Lumens:** 712

**Length:** 3.94 IN

**Operating Position:** Universal

**Package Weight:** 1.60 L

**Shape:** A19

**Type:** Incandescent

**Voltage:** 120-130 V

ULEPH,ROHS,NSF Splash Zone