



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



074011266 STR Male, DCG, 2.3-2.4", 2 1/2" W/Mesh *Hubbell Wiring Devices*

Catalog Number	074011266
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Deluxe Cord Grips, Straight Male, 2.312-2.437", 2 1/2" With Mesh
Weight per unit	2.0 (lbs/each)
Product Category	Cable & Cord Grips

Features

Material	Aluminum Fittings, Stainless Steel Mesh
Number of Conductors	Single

Material, Color, and Finish

Color	Metallic
-------	----------

Dimensions and Weight

Size	2 1/2" NPT
------	------------

Descriptions

Description	STR MALE, DCG, 2.3-2.4", 2 1/2" W/MESH
extra long description	HWDK 074011266 STR MALE, DCG, 2.3-2
Features	Deluxe cord grips help to alleviate pull tension on terminals, control cable arc-of-bend, prevent cord pull-out and provide a Liquidtight seal. They are offered with either aluminum, stainless steel or nylon fittings in a variety of configurations and NPT thread sizes. Additionally, a completely non-metallic product is available. Specific uses are: wiring enclosures, pendant stations, hand tools, construction, processing and material handling equipment, pumps, motors and machine tools.
Long Description	Kellems Wire Management, Deluxe Cord Grips, Straight Male, 2.312-2.437", 2 1/2" with Mesh
Product Type	STR Male, DCG, 2.3-2.4", 2 1/2" W/Mesh
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585498669
Manufacturers Part Number	074011266
series	Deluxe Cord Grips
UPC	783585498669

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Straight Male Thread



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2

Uses, Certifications, and Standards

Application	Straight Male- Form 7
environmental conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Mounting	Locknut or Tapped Opening
standard	UL Listed
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)