



PRODUCT CODE	PART NUMBER	NOMINAL SIZE		A		A1		B	
		(in)	(mm)	(in)	(mm)	(in)	(mm)	(in)	(mm)
078276	JBA05	1/2	16	0.840	21	0.605	15	1.210	31
078277	JBA07	3/4	21	1.050	27	0.800	20	1.400	36
078278	JBA10	1	27	1.310	33	1.000	25	1.580	40
078279	JBA12	1 1/4	35	1.655	42	1.355	34	1.975	50
078280	JBA15	1 1/2	41	1.900	48	1.560	40	2.350	60
078281	JBA20	2	53	2.370	60	2.050	52	2.845	72
078282	JBA25	2 1/2	63	2.865	73	2.450	62	3.375	86
078283*	JBA30	3	76	3.500	89	3.040	77	3.960	101
078284*	JBA35	3 1/2	91	4.000	101	3.480	88	4.490	114
078285*	JBA40	4	103	4.500	115	4.016	102	5.000	127

PRODUCT CODE	PART NUMBER	NOMINAL SIZE		L		L1	
		(in)	(mm)	(in)	(mm)	(in)	(mm)
078276	JBA05	1/2	16	0.900	23	1.050	27
078277	JBA07	3/4	21	1.000	25	1.150	29
078278	JBA10	1	27	0.890	23	1.060	27
078279	JBA12	1 1/4	35	1.125	29	1.325	34
078280	JBA15	1 1/2	41	1.100	30	1.370	35
078281	JBA20	2	53	1.255	32	1.560	40
078282	JBA25	2 1/2	63	1.843	47	2.156	55
078283*	JBA30	3	76	2.020	51	2.380	61
078284*	JBA35	3 1/2	91	1.975	50	2.300	58
078285*	JBA40	4	103	2.375	60	2.687	68

* Not UL Listed