



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



091548808 4' 4 Wire Dryer Cord 10-4 *Southwire Company*

| | |
|------------------|-----------------------|
| Catalog Number | 091548808 |
| Manufacturer | Southwire Company |
| Description | 10/4 30A Dryer BLK 4' |
| Weight per unit | 2.1 (lbs/ft) |
| Product Category | Portable Cord Sets |

Features

| | |
|----------------------|--------------|
| amperage rating | 30 |
| Conductor Size | 10 |
| connection | 14-30 |
| core | PVC |
| Number of Conductors | 4 |
| outside diameter | 0.67 |
| Resistance | -20 to +60 C |
| strands | 104/30 |
| Voltage Rating | 125/250 |

Material, Color, and Finish

| | |
|---------------------|--------|
| Color | Black |
| Conductor Material | Copper |
| Insulation Material | PVC |
| Jacket Material | PVC |

Dimensions and Weight

| | |
|--------|---|
| Length | 4 |
|--------|---|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 4' 4 WIRE DRYER CORD 10-3 |
| extra long description | SWC 9154SW8808 CORD, DRYER 10/4 30A |
| Long Description | 10/4 30A DRYER BLK 4' |
| Product Type | Cord, Dryer 10/4 30A Black 4' 6PK |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Cables & Cords |
| GTIN | 00029892091545 |
| Manufacturers Part Number | 9154SW8808 |
| UPC | 029892091545 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | CORD SETS [DRYER & RANGE CORDS & BOOSTER CABLES] |
| Type | Cord Set |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 6 |
| Weight | 1.6 |
| Weight Per foot | 2.1219 |

Uses, Certifications, and Standards

| | |
|--------------------|----------------|
| Application | Extension Cord |
| standard | UL817 |
| Temperature Rating | -20 to +60 C |