



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## OLVTWMM6 Wall MNT Vap Tite FXT

*Lithonia Lighting - Acuity*

Catalog Number	OLVTWMM6
Manufacturer	Lithonia Lighting - Acuity
Description	Energy-Efficient Solution For Environments Where Some Protection From Dust and Moisture and Larger Objects Is Required
Weight per unit	2.9 (lbs/each)
Product Category	Led Vapor Tight Lighting

### Features

Ballast Type	Not Applicable
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	600 LM
Material	Aluminum
Number of Lamps	Not Applicable
pallet quantity	144
Power Source	Hardwired
Shape	OVAL
Socket Type	Not Applicable
Voltage Rating	MVOLT
Warranty	5
Wattage	15

### Material, Color, and Finish

Color	Gray
color rendering index (cri)	74
color temperature	4000
fixture material	aluminum
Lens Material	Glass
Style	Traditional

### Dimensions and Weight

Height	11.25
Length	7.375
Width	4.625



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	WALL MNT VAP TITE FXT
extra long description	LITH OLVTWM M6 LED vapor tight wall
Long Description	Energy-efficient solution for environments where some protection from dust and moisture and larger objects is required
Product Type	Wallpack
Special Features	Provides years of maintenance-free illumination for indoor or outdoor use in residential and commercial applications.

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00753573237457
Manufacturers Part Number	OLVTWM M6
UPC	753573237457

## Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	AREA LIGHT

## Packaging

Carton	1
Weight	3.5
Weight Per each	2.9

## Uses, Certifications, and Standards

Application	Warehouses
environmental conditions	OUTDOOR
Mounting	SURFACE
standard	UL