



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Heavy-Duty Pushbutton Operator

10250T112

UPC:782113203348

### Dimensions:

- **Height:** 2.1 IN
- **Length:** 1.9 IN
- **Width:** 1.9 IN

**Weight:** .35 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Extended
- **Actuator Color:** Red
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Illumination:** Non-illuminated
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T112](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked





Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Heavy-Duty Pushbutton Operator

10250T112

UPC:782113203348

### Dimensions:

- **Height:** 2.1 IN
- **Length:** 1.9 IN
- **Width:** 1.9 IN

**Weight:** .35 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Extended
- **Actuator Color:** Red
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Illumination:** Non-illuminated
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T112](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked

