

# Eaton 10250T15712

Catalog Number: 10250T15712

Eaton 10250T, Selector switch, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, Left only, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton 10250T pushbutton	10250T15712
<b>UPC</b>	<b>Product Length/Depth</b>
782113312613	2 in
<b>Product Height</b>	<b>Product Width</b>
2.2 in	1.8 in
<b>Product Weight</b>	<b>Warranty</b>
0.4 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed
	CSA Certified

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Heavy-Duty

### Cam code

Cam 1

### Key removal position

Left only

### Product Category

Selector switch

### Actuator

Key operated

### Throw type

60 °

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Number of positions

2

### Series

10250T

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Cam selection for pushbutton selectors

Eaton Specification Sheet - 10250T15712



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia