

# Eaton 10250T20KB-POP

Catalog Number: 10250T20KB-POP

10250T, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Knob, Black actuator, OFF/ON HAND/AUTO RUN/JOG, 1NO-1NC

## General specifications



### Product Name

Eaton 10250T pushbutton

### Catalog Number

10250T20KB-POP

### UPC

782114408506

### Product Length/Depth

7 in

### Product Height

3 in

### Product Width

6 in

### Product Weight

0.43 lb

### Warranty

1 year

### Compliances

CE Marked

### Certifications

UL Listed

CSA Certified

### Catalog Notes

Includes three different legend plates.

Point-of-Purchase Packaging.

**Type**

30.5 mm, Heavy-Duty

**Actuator color**

Black

**Legend**

OFF/ON HAND/AUTO RUN/JOG

**Actuator**

Knob

**Illumination**

Non-illuminated

**Number of positions**

2

**Rating**

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

**Series**

10250T

**Contact configuration**

1 NO-1 NC

**Catalogs**

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

**Multimedia**

[How to size and select a Power Supply](#)

**Specifications and datasheets**

[Quick Selector - 10250T Pilot Devices](#)

[Eaton Specification Sheet - 10250T20KB-POP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)