

Eaton 10250T411

Catalog Number: 10250T411

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Incandescent, transformer light unit, Flush, 120 V light unit, Chrome bezel, #755



General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T411
UPC	Product Length/Depth
782113203713	2.4 in
Product Height	Product Width
3.4 in	2.1 in
Product Weight	Warranty
0.35 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

10250T series

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Bezel

Chrome

Operating mode

Momentary

Illumination

Illuminated

Series

10250T

LED lamp number

#755

Light unit type

Incandescent, transformer

Light unit voltage

120 Vac

Mounting method

Flush

Rating

NEMA 12

NEMA 4X

NEMA 3

NEMA 13

NEMA 4

NEMA 3R

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T411



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)