



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1104B DPST 40A Time Switch

*Nsi Industries*

Catalog Number	1104B
Manufacturer	Nsi Industries
Description	Time Switch, Metal Enclosure Material, 24 H Time Setting Mode, 75 (Min) Off;20 (Min) On Time Setting, 24 H Time Setting, DPST Contact Configuration, 208 to 277 V Ac @ 60 HZ, 40 A, Screw Connection, Metal Material, -40 °F Operating Temperature, +165 °F Operating Temperature, 4-11/16 X 2-15/16 X 7-15/16 In Size, 2.4 LB
Weight per unit	2.4 (lbs/each)
Product Category	Mechanical Time Switches

### Features

action	DPST
Base	Screw
Contact Rating	208-277 VAC
Number of Pins	12 Pair
Phase	Single Phase
Poles	1
Timing Range	24 Hour

### Descriptions

Description	DPST 40A TIME SWITCH
extra long description	TORK 1104B 24 Hour Time Switch 40A
Features	24 Hour Time Switch 40A 208-277V DPST Indoor Metal Enclosure
Special Features	DPST 24 Hour Time Switch - Same Day On-Off Times Each Day

### Manufacturer Information

GTIN	00786261100672
UPC	786261100672

### Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	24 Hour Time Switch

### Packaging

Carton	1
Weight Per each	2.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Enclosure	NEMA 1 Metal Indoor
environmental conditions	-40 to 165 F
Frequency Rating	60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to 165 F
standard	UL-CSA