



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1104B0 277V Time Switch Case

*Nsi Industries*

Catalog Number	1104B0
Manufacturer	Nsi Industries
Description	Time Switch, Metal Enclosure Material, 24 H Time Setting Mode, 75 (Min) Off;20 (Min) On Time Setting, 24 H Time Setting, DPST Contact Configuration, 208 to 277 V Ac, 40 A, Metal Material, -40 °F Operating Temperature, +165 °F Operating Temperature, 5-1/4 X 3-1/4 X 8-1/4 In Size, 3.9 LB
Weight per unit	3.9 (lbs/each)
Product Category	Mechanical Time Switches

### Features

action	DPST
Base	Screw
Contact Rating	208-277 VAC
Number of Pins	12 Pair
Phase	Single Phase
Poles	1
Timing Range	24 Hour

### Descriptions

Description	277V TIME SWITCH CASE
Special Features	DPST 24 Hour Time Switch - Same Day On-Off Times Each Day

### Manufacturer Information

GTIN	00786261100757
Manufacturers Part Number	1104B-O
UPC	786261100757

### Taxonomies, Classifications, and Categories

Type	24 Hour Time Switch
------	---------------------

### Availability

Manufacturer Status	Inactive
Status	Inactive

### Packaging

Carton	1
Weight Per each	3.9



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Enclosure	NEMA 3 Metal Indoor/Outdoor
environmental conditions	-40 to 165 F
Frequency Rating	60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to 165 F
standard	UL-CSA