



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



11100R6513 Comet Thru-Beam Source Wide Angle Right Angle Ac/D

Eaton Corp

Catalog Number	11100R6513
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Through Beam, Wide Right, Power, 6.6 FT, PVC, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN)
Weight per unit	0.7000 (lbs/each)
Product Category	Sensor Accessories

Dimensions and Weight

Height	0.71
Length	2.55
Width	0.47

Descriptions

Description	COMET THRU-BEAM SOURCE WIDE ANGLE RIGHT ANGLE AC/D
extra long description	ETN 11100R6513 18MM TB SOURCE RA,20
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor,Through Beam, Wide right, Power, 6.6 ft, PVC, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
Product Type	18MM TB Source Ra, 20-264VACDC, 6' CBL

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113819204
Manufacturers Part Number	11100R6513
UPC	782113819204

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	0.7

Uses, Certifications, and Standards

Application	Vehicles: On-Road - PickUp & Delivery: Food
Operating Temperature standard	-4° to 158°F (-20° to 70°C) UL Recognized,cUL Recognized