



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1135CLBZ 3-60C BZ Knoxville 19" Outdoor WMNT *Maxim Lighting*

Catalog Number	1135CLBZ
Manufacturer	Maxim Lighting
Description	Knoxville Is An Updated Take On The Traditional Lantern Style. Finished In Bronze and With The Option Of Clear or Frosted Glass, Our Incandescent Version Is Sure to Wow.
Weight per unit	7.0 (lbs/each)
Product Category	Lighting

Features

bulb type	B10
Category	Exterior
Safety Rating	Wet
Voltage	120.00 LBS

Material, Color, and Finish

Finish	Bronze/Dark
Style	Transitional

Descriptions

Description	3-60C BZ KNOXVILLE 19" OUTDOOR WMNT
Long Description	Knoxville is an updated take on the traditional lantern style. Finished in Bronze and with the option of Clear or Frosted glass, our Incandescent version is sure to wow.
Product Type	Three Light Outdoor Wall Lantern

Manufacturer Information

Brand	Maxim
GTIN	00783209138469
Manufacturers Part Number	1135CLBZ
UPC	783209138469

Taxonomies, Classifications, and Categories

Category Description	DECORATIVE RESIDENTIAL
Type	WALL MOUNT

Packaging

Carton	1
Weight Per each	7