

# Eaton 12106-SDFQR

Catalog Number: 12106-SDFQR

Eaton B-Line series JIC panel enclosure, 11.42" height, 6.31" length, 11.83" width, NEMA 4X, Hinged cover, SDFQR enclosure, Wall mount, Medium single door, Optional external mounting feet, Fiberglass, Seamless poured in-place gasket

## General specifications

|   |                      |
|---|----------------------|
| Product Name                            | Catalog Number       |
| Eaton B-Line series JIC panel enclosure | 12106-SDFQR          |
| UPC                                     | Product Length/Depth |
| 782051524291                            | 6.31 in              |
| Product Height                          | Product Width        |
| 11.42 in                                | 11.83 in             |
| Product Weight                          | Certifications       |
| 6 lb                                    | UL 50                |
|   | NEMA                 |
|   | CSA C22.2.           |

## Material/finish

### Material

Fiberglass

### Finish color

Unfinished

### Color

Gray

## Model

### Style

Medium single door

### Model

SDFQR enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

Optional external mounting feet

### Locking provisions

Padlock provision

### Closure type

Hinged

### Special features

Stainless pull drawn catch

## Standards

### NEMA Rating

4X

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 12106-SDFQR](#)