



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



121248GNK 12X12X48 Wireway

Unity MFG

Catalog Number	121248GNK
Manufacturer	Unity MFG
Description	Unity 121248GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 48 In, Width: 12 In, 12 In Height, Nema 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 Ga Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/Us UI 50 and UI 870 - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 26 Certified, Type 1, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Terminatio
Weight per unit	40.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

Cover Type	Removable Hinged
Knockouts	NO
Material	Low-Carbon Steel

Material, Color, and Finish

Finish	Powder Coat
--------	-------------

Dimensions and Weight

Height	12
Length	48
Width	12



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Formed From Code Gauge, Low Carbon Steel
Description	12X12X48 WIREWAY
extra long description	UNT 121248GNK N1 HINGED COVER WIREW
Long Description	Unity 121248GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 48 IN, Width: 12 IN, 12 IN Height, NEMA 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 GA Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Terminatio
Product Type	N1 Hinged Cover Wireway No K.O. Powder Coated
Special Features	For protecting electrical wiring where dust, dirt, oil and water are not serious problems; All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run; No pulling-through of wires or cables is required; Wireway body has mounting holes on the back; Cover is secured to the body with plated screws; Keyhole slots are furnished on the wireway cover which allow easy access to the inside without removing the screws

Manufacturer Information

Brand	Unity
GTIN	00761515107201
Manufacturers Part Number	121248GNK
UPC	761515107201

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Lay-In Wireway

Packaging

Carton	1
Weight Per each	40



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For Cable And Wire Junction, Distribution And Termination, Houses Runs Of Control And Power Cable
Enclosure standard	NEMA 1, IP30 C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant