

Eaton 1225

Catalog Number: 1225

Eaton power device receptacle, #12 - 4 AWG, 30A, Surface, 125/250V, Back, Black, NEMA 14-30R, Three-pole, Four-wire, Three-pole, four-wire, grounding, Screw, Glass-filled nylon, Power



General specifications

Product Name	Catalog Number
Eaton power device receptacle	1225
UPC	Product Length/Depth
032664305702	2.25 in
Product Height	Product Width
10 in	5 in
Product Weight	Certifications
0.82 lb	CSA Certified
	NOM
	cULus Listed

Product specifications

Color

Black

Wiring method

Back

Material

Glass filled nylon

Mounting method

Surface

Allowable wire size

#12-4 AWG

Amperage Rating

30A

Number Of Poles

Three-pole

NEMA configuration

14-30R

Design type

Receptacle

Connection type

Screw

Style

Power

Number of wires

4

Receptacle type

Three-pole, four-wire, grounding

Voltage rating

125/250 V

Resources

Brochures

[Flush mount receptacles sell sheet](#)

[Wiring Devices Buyer's Guide](#)

Catalogs

[Residential Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 1225](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)