

Eaton 1234-BOX

Catalog Number: 1234-BOX

Eaton power device receptacle, #12 - 4 AWG, 30A, Flush, 250V, Back, Black, NEMA 6-30R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with S42



General specifications

Product Name	Catalog Number
Eaton power device receptacle	1234-BOX
UPC	Product Length/Depth
032664306303	2.25 in
Product Height	Product Width
3.88 in	2.38 in
Product Weight	Compliances
0.36 lb	RoHS Compliant
	NAFTA
Certifications	
UL Listed	
NOM	
CSA Certified	

defaultTaxonomyAttributeLabel

Used with

S42

Amperage Rating

30A

Voltage rating

250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Color

Black

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

6-30R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 1234-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia