



LOCKING MANUAL CONTROLLER

1250L | [Pass & Seymour](#)

FEATURES & BENEFITS

Single Pole, Double Throw Switch. 15 Amps, 120/277VAC rating, Locking.

Tested to 3 Amps, 24Vdc rating.



- Oversize silver alloy contacts for long life and better heat dissipation.
- Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
- Fiber terminal insulation barriers standard.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Bodies, covers, and toggles molded of durable nylon.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Locking Switches supplied with one 1498-NT key.
- Normally open.

SPECIFICATIONS

GENERAL INFO

Type: Momentary Contact

Number Of Poles: 1

Special Features: Three Position

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: Yes

UL Listing No: Yes

UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.469"
Height (US): 3.281"
Width (US): 1.5"
Weight: 0.26216

TECHNICAL INFORMATION

Amps: 15A
Volts: 120/277VAC
Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant





LOCKING MANUAL CONTROLLER

1250L | [Pass & Seymour](#)

FEATURES & BENEFITS

Single Pole, Double Throw Switch. 15 Amps, 120/277VAC rating, Locking.

Tested to 3 Amps, 24Vdc rating.



- Oversize silver alloy contacts for long life and better heat dissipation.
- Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
- Fiber terminal insulation barriers standard.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Bodies, covers, and toggles molded of durable nylon.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Locking Switches supplied with one 1498-NT key.
- Normally open.

SPECIFICATIONS

GENERAL INFO

Type: Momentary Contact

Number Of Poles: 1

Special Features: Three Position

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: Yes

UL Listing No: Yes

UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.469"
Height (US): 3.281"
Width (US): 1.5"
Weight: 0.26216

TECHNICAL INFORMATION

Amps: 15A
Volts: 120/277VAC
Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

