
MANUAL CONTROLLER

1251W | [Pass & Seymour](#)



FEATURES & BENEFITS

Single Pole, Double Throw Manual Control Switch, 20 amps, 120/277 volts, White.



Oversize silver alloy contacts for long life and better heat dissipation. Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. Fiber terminal insulation barriers standard. Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. Bodies, covers, and toggles molded of durable nylon. Single Pole-Double Throw and Double Pole-Double Throw. Locking Switches supplied with one 1498-NT key. Normally open.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Momentary Contact
Number Of Poles: 1
Special Features: Three Position

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
UL Listing No: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.469"
Height (US): 3.281"
Width (US): 1.5"
Weight: 0.0288

TECHNICAL INFORMATION

Amps: 20A

Volts: 120/277VAC

Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

