

Eaton 1257-SP

Catalog Number: 1257-SP

Eaton power device receptacle, Dryer, #12 - 4 AWG, 30A, Flush, 125/250V, Back, Black, NEMA 14-30R, Three-pole, Four-wire, Three-pole, four-wire, grounding, Screw, Glass-filled nylon, Power, Used with S21



General specifications

Product Name	Catalog Number
Eaton power device receptacle	1257-SP
UPC	Product Length/Depth
032664306808	2.5 in
Product Height	Product Width
8.5 in	5 in
Product Weight	Compliances
0.3 lb	RoHS Compliant
	NAFTA
Certifications	
UL Listed	
CSA Certified	
NOM	

defaultTaxonomyAttributeLabel

Used with

S21

Special features

Dryer

Amperage Rating

30A

Voltage rating

125/250 V

Wiring method

Back

Number of wires

4

Mounting method

Flush

Number Of Poles

Three-pole

Color

Black

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

14-30R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Three-pole, four-wire, grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 1257-SP](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton 1257-SP

Catalog Number: 1257-SP

Eaton power device receptacle, Dryer, #12 - 4 AWG, 30A, Flush, 125/250V, Back, Black, NEMA 14-30R, Three-pole, Four-wire, Three-pole, four-wire, grounding, Screw, Glass-filled nylon, Power, Used with S21



General specifications

Product Name	Catalog Number
Eaton power device receptacle	1257-SP
UPC	Product Length/Depth
032664306808	2.5 in
Product Height	Product Width
8.5 in	5 in
Product Weight	Compliances
0.3 lb	RoHS Compliant
	NAFTA
Certifications	
UL Listed	
CSA Certified	
NOM	

defaultTaxonomyAttributeLabel

Used with

S21

Special features

Dryer

Amperage Rating

30A

Voltage rating

125/250 V

Wiring method

Back

Number of wires

4

Mounting method

Flush

Number Of Poles

Three-pole

Color

Black

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

14-30R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Three-pole, four-wire, grounding

Resources

Brochures

Flush mount receptacles sell sheet

Catalogs

Arrow Hart Buyers Guide Section B

Specifications and datasheets

Eaton Specification Sheet - 1257-SP



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia