




**BOX COVERS &
CONDUIT BODIES**



WEATHERPROOF




METAL WALLPLATES



**UNBREAKABLE
THERMOPLASTIC
WALLPLATES**



Mulberry Metal Products, Inc.
2199 Stanley Terrace
P.O. Box 443
Union, New Jersey 07083
tel. 908.688.8850
fax. 908.688.7294
www.mulberrymetal.com



**Die-Cast Aluminum
Conduit Bodies**

Threaded
Set-Screw
Combination
SLBs
Moguls
Covers
Gaskets

Conduit Bodies

Threaded, Set Screw, and Combination Bodies and Kits



Hub Size	Unassembled (body only)			Assembled (with cover and gasket)			Box Quantity	Carton Quantity
	Threaded	Catalog No. Set Screw	Combination	Threaded	Catalog No. Set Screw	Combination		
LB								
1/2"	11801	11851	13801	12801	12851	14801	10	50
3/4"	11802	11852	13802	12802	12852	14802	10	50
1"	11803	11853	13803	12803	12853	14803	5	25
1 1/4"	11804	11854	13804	12804	12854	14804	—	2
1 1/2"	11805	11855	13805	12805	12855	14805	—	2
2"	11806	11856	13806	12806	12856	14806	—	1
2 1/2"				12807	12857		—	1
3"				12808	12858		—	1
3 1/2"				12809			—	1
4"				12810			—	1
LL								
1/2"	11811	11861	13811	12811	12861	14811	10	50
3/4"	11812	11862	13812	12812	12862	14812	10	50
1"	11813	11863	13813	12813	12863	14813	5	25
1 1/4"	11814	11864	13814	12814	12864	14814	—	2
1 1/2"	11815	11865	13815	12815	12865	14815	—	2
2"	11816	11866	13816	12816	12866	14816	—	1
2 1/2"				12817			—	1
3"				12818			—	1
3 1/2"				12819			—	1
4"				12820			—	1
LR								
1/2"	11821	11871	13821	12821	12871	14821	10	50
3/4"	11822	11872	13822	12822	12872	14822	10	50
1"	11823	11873	13823	12823	12873	14823	5	25
1 1/4"	11824	11874	13824	12824	12874	14824	—	2
1 1/2"	11825	11875	13825	12825	12875	14825	—	2
2"	11826	11876	13826	12826	12876	14826	—	1
2 1/2"				12827			—	1
3"				12828			—	1
3 1/2"				12829			—	1
4"				12830			—	1
G								
1/2"	11831	11881	13831	12831	12881	14831	10	50
3/4"	11832	11882	13832	12832	12882	14832	10	50
1"	11833	11883	13833	12833	12883	14833	5	25
1 1/4"	11834	11884	13834	12834	12884	14834	—	2
1 1/2"	11835	11885	13835	12835	12885	14835	—	2
2"	11836	11886	13836	12836	12886	14836	—	1
2 1/2"				12837			—	1
3"				12838			—	1
T								
1/2"	11841	11891	13841	12841	12891	14841	10	50
3/4"	11842	11892	13842	12842	12892	14842	10	50
1"	11843	11893	13843	12843	12893	14843	5	25
1 1/4"	11844	11894	13844	12844	12894	14844	—	2
1 1/2"	11845	11895	13845	12845	12895	14845	—	2
2"	11846	11896	13846	12846	12896	14846	—	1
2 1/2"				12847			—	1
3"				12848			—	1

Conduit Bodies

SLBs and Moguls



Catalog No.	Hub Size	Box Quantity	Carton Weight per Quantity	100 Units
SLBs				
11901	1/2"	10	50	24 lbs.
11902	3/4"	10	50	30 lbs.
11903	1"	5	25	55 lbs.
11904	1 1/4"	—	1	140 lbs.
11905	1 1/2"	—	1	150 lbs.
11906	2"	—	1	260 lbs.

MOGUL CONDUIT BODIES COMPLETE WITH COVER, GASKET, AND SCREWS


11914	1 1/4"	5	130 lbs.
11915	1 1/2"	2	350 lbs.
11916	2"	2	310 lbs.



Conduit Fitting Covers and Gaskets

Oval-Round F-35 Series, 1/2" - 4"

Catalog No.	Old No.	Description	Box Quantity	Carton Quantity	Weight Per 100 Units
GALVANIZED STEEL — 1/2 - 4"					
11699	1/2F35C	Blank, 1/2"	25	250	10 lbs.
11700	3/4F35C	Blank, 3/4"	25	250	13 lbs.
11701	1F35C	Blank, 1"	20	200	15 lbs.
11702	1-1/4F35C	Blank, 1 1/4"-1 1/2"	—	25	32 lbs.
11703	2F35C	Blank, 2"	—	25	51 lbs.
11704	3F35C	Blank, 2 1/2"-3"	—	25	88 lbs.
11705	4F35C	Blank, 3 1/2"-4"	—	25	142 lbs.
ALUMINUM — 1/2 - 4"					
11710	1/2AF35C	Blank, 1/2"	25	250	4 lbs.
11711	3/4AF35C	Blank, 3/4"	25	250	5 lbs.
11712	1AF35C	Blank, 1"	20	200	7 lbs.
11713	1-1/4AF35C	Blank, 1 1/4"-1 1/2"	—	25	13 lbs.
11714	2AF35C	Blank, 2"	—	25	25 lbs.
11715	3AF35C	Blank, 2 1/2"-3"	—	25	36 lbs.
11716	4AF35C	Blank, 3 1/2"-4"	—	25	66 lbs.
GASKETS — 1/2 - 4"					
11720	1/2F35G	Full, 1/2"	100	1000	2 lbs.
11721	3/4F35G	Full, 3/4"	100	1000	2 lbs.
11722	1F35G	Full, 1"	50	500	3 lbs.
11723	1-1/4F35G	Full, 1 1/4"-1 1/2"	—	600	5 lbs.
11724	2F35G	Full, 2"	—	400	7 lbs.
11725	3F35G	Full, 2 1/2"-3"	—	200	14 lbs.
11726	4F35G	Full, 3 1/2"-4"	—	150	20 lbs.



No. 11699 No. 11720

