



Minute Mend™ Epoxy Putty, 4 Wt Oz

No. 14070 | Item# 1004796 | Case# 1004795

Product Description	This two part epoxy permanently repairs scratches, gouges and holes. Bonds to wood, steel, fiberglass, glass, ceramics, plastics, concrete and aluminum. Also bonds to both wet and dry surfaces. It is ready to use in less than one minute.
Applications	Drums, tanks, castings, molds, sinks, tubs, gaskets, mounting terminal blocks, packing wires & repairing breaker boxes
Unit Package Description	4 ounce Stick
Brand	CRC
Generic Description 1	Epoxy Putty
Net Fill	4 Wt Oz
UPC Code	078254140704
Unit Dimensions	8H x 1W x 1D in
Units Per Case	24
Case Dimensions	9.06H x 5.5W x 7.13D in
Cases Per Pallet	144
Case Weight	8 lbs
I 2 of 5 Code	30078254140705
Appearance	Green and White Putty
Flash point (F)	>200°F
Flash point (C)	>93.3°C
Flammability Class - CPSC	None
Spec Gravity Concentrate	1.97
Plastic Safe	Safe on Most Plastics (Test small area)
Evaporation Rate	Negligible
Curing Time	24 Hours
Dielectric Strength	300 Volts/Mil
Working Temp (F)	250°F (Continuous) / 350°F (Intermittent)
Working Temp (C)	121°C (Continuous) / 176.66°C (Intermittent)

Last revised: 10/8/2019

Page 1 of 2



Chemical Solutions to Keep You Moving™

f t+ d in • 800-272-8963 • crcindustries.com



Propellant	None
DOT Proper Shipping Name	Not Regulated
VOC % (Consumer Product def)	0
VOC g/L (Consumer Product def)	0
VOC lbs/gal (Consumer Prod def)	0
VOC Category	Sealant or Caulking Compound, chemically curing, nonaerosol
Removal (How To)	Cured Material: Heat to Soften