



149	4"	10.25	12.50	4.350	5.440
148	3 1/2"	10.25	12.50	4.350	4.950
147	3"	8.50	10.50	3.375	4.500
146	2 1/2"	8.25	9.37	2.665	3.830
145	2"	6.00	6.62	2.093	2.920
144	1 1/2"	4.37	4.87	1.500	2.093
143	1 1/4"	3.37	4.25	1.550	2.270
142	1"	3.12	3.62	1.187	1.700
141	3/4"	2.80	3.12	.915	1.460
140	1/2"	2.65	2.65	.675	1.250
PART NO.	TRADE SIZE	"A"	"B"	MIN	MAX