



Powering Business Worldwide

pe.eaton.com

Fiber Optic Cable

1450B-6501

UPC:782113824697

Dimensions:

- **Height:** 1.64 IN
- **Length:** 3.19 IN
- **Width:** 1.83 IN

Warranties:

- 3 year

Specifications:

- **Type:** Accessory
- **Connection:** Mini
- **Diameter:** .03937008 MM
- **Enclosure Material:** Noryl
- **Environmental Rating:** NEMA 1, 3, 4, 12, 13
- **Input Voltage:** 115V
- **Number Of Pins:** 5 pin
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Sensor Type:** Retroreflective
- **Used With:** Used with photoelectric sensors

Supporting documents:

- [Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 1450B-6501](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Fiber Optic Cable

1450B-6501

UPC:782113824697

Dimensions:

- **Height:** 1.64 IN
- **Length:** 3.19 IN
- **Width:** 1.83 IN

Warranties:

- 3 year

Specifications:

- **Type:** Accessory
- **Connection:** Mini
- **Diameter:** .03937008 MM
- **Enclosure Material:** Noryl
- **Environmental Rating:** NEMA 1, 3, 4, 12, 13
- **Input Voltage:** 115V
- **Number Of Pins:** 5 pin
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Sensor Type:** Retroreflective
- **Used With:** Used with photoelectric sensors

Supporting documents:

- [Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 1450B-6501](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

