



Powering Business Worldwide

### 145-BOX

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664481000

Brand Name: Eaton  
Sub Brand: EATON  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Back and Side Wire  
Application: Surface mount & power  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 250 Vac  
Material: Heavy Duty Plastic Construction  
Color: Ivory  
NEMA Rating: 6-15R  
Mounting: Wall  
Connection: Screw  
Size: 1.21X 1.90 X3.60 IN  
Environmental Conditions: Wall  
Dielectric Strength: 250 vac  
Insulation: Nylon Face  
Temperature Rating: -20C to 70C (-4F to 158F)

### BP145

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664103605

Brand Name: Cooper Wiring Devices  
Type: (1) Dimmer, (1) 3 Speed Fan Controller  
Voltage Rating: 120 Vac  
Amperage Rating: 1.5 Amp  
Wattage: 300 W  
Load: Incandescent, Halogen  
Number Of Poles: 1  
Size: 1.63 In Width  
Connection: Wire Lead  
Operating Temperature: 0 To 40 Deg C



Powering Business Worldwide

### 145-BOX

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664481000

Brand Name: Eaton  
Sub Brand: EATON  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Back and Side Wire  
Application: Surface mount & power  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 250 Vac  
Material: Heavy Duty Plastic Construction  
Color: Ivory  
NEMA Rating: 6-15R  
Mounting: Wall  
Connection: Screw  
Size: 1.21X 1.90 X3.60 IN  
Environmental Conditions: Wall  
Dielectric Strength: 250 vac  
Insulation: Nylon Face  
Temperature Rating: -20C to 70C (-4F to 158F)

### BP145

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664103605

Brand Name: Cooper Wiring Devices  
Type: (1) Dimmer, (1) 3 Speed Fan Controller  
Voltage Rating: 120 Vac  
Amperage Rating: 1.5 Amp  
Wattage: 300 W  
Load: Incandescent, Halogen  
Number Of Poles: 1  
Size: 1.63 In Width  
Connection: Wire Lead  
Operating Temperature: 0 To 40 Deg C