



Powering Business Worldwide

145-BOX

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664481000

Brand Name: Eaton

Sub Brand: EATON

Type: Duplex, Straight Blade

Special Features: Wiring Type Back and Side Wire

Application: Surface mount & power

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 250 Vac

Material: Heavy Duty Plastic Construction

Color: Ivory

NEMA Rating: 6-15R

Mounting: Wall

Connection: Screw

Size: 1.21X 1.90 X3.60 IN

Environmental Conditions: Wall

Dielectric Strength: 250 vac

Insulation: Nylon Face

Temperature Rating: -20C to 70C (-4F to 158F)

BP145

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664103605

Brand Name: Cooper Wiring Devices

Type: (1) Dimmer, (1) 3 Speed Fan Controller

Voltage Rating: 120 Vac

Amperage Rating: 1.5 Amp

Wattage: 300 W

Load: Incandescent, Halogen

Number Of Poles: 1

Size: 1.63 In Width

Connection: Wire Lead

Operating Temperature: 0 To 40 Deg C



Powering Business Worldwide

145-BOX

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664481000

Brand Name: Eaton

Sub Brand: EATON

Type: Duplex, Straight Blade

Special Features: Wiring Type Back and Side Wire

Application: Surface mount & power

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 250 Vac

Material: Heavy Duty Plastic Construction

Color: Ivory

NEMA Rating: 6-15R

Mounting: Wall

Connection: Screw

Size: 1.21X 1.90 X3.60 IN

Environmental Conditions: Wall

Dielectric Strength: 250 vac

Insulation: Nylon Face

Temperature Rating: -20C to 70C (-4F to 158F)

BP145

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664103605

Brand Name: Cooper Wiring Devices

Type: (1) Dimmer, (1) 3 Speed Fan Controller

Voltage Rating: 120 Vac

Amperage Rating: 1.5 Amp

Wattage: 300 W

Load: Incandescent, Halogen

Number Of Poles: 1

Size: 1.63 In Width

Connection: Wire Lead

Operating Temperature: 0 To 40 Deg C