



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



14RB8F Ins Vinyl Fork Term 18-14 NO8 Blue

Abb Installation Products, Inc

| | |
|------------------|---|
| Catalog Number | 14RB8F |
| Manufacturer | Abb Installation Products, Inc |
| Description | Vinyl-Insulated Fork Terminal, Length .97 Inches, Width .31 Inches, Maximum Insulation .170, Bolt Hole #8, Wire Range #18-#14 Awg, Color Blue, Copper, Tin Plated |
| Weight per unit | 0.0010 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|-----------|
| Material | Copper |
| Voltage Rating | 600 V |
| Wire Size | 18-14 AWG |

Material, Color, and Finish

| | |
|-------|------|
| Color | Blue |
|-------|------|

Descriptions

| | |
|------------------------|--|
| Description | INS VINYL FORK TERM 18-14 NO8 BLUE |
| extra long description | ABB 14RB-8F INS VINYL FORK TERM 18- |
| Long Description | Vinyl-Insulated Fork Terminal, Length .97 Inches, Width .31 Inches, Maximum Insulation .170, Bolt Hole #8, Wire Range #18-#14 AWG, Color Blue, Copper, Tin Plated |
| Product Type | Ins Vinyl Fork Term 18-14 NO8 Blue |
| Special Features | These fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wires flex point. Brazed seam barrel is serrated for high pull-out value. Insulation is color-coded |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Sta-Kon |
| GTIN | 00786210800660 |
| Manufacturers Part Number | 14RB-8F |
| UPC | 786210800660 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | TERMINALS |
| Type | Vinyl Insulated Fork Terminal |

Packaging

| | |
|-----------------|-------|
| Carton | 100 |
| Weight Per each | 0.001 |

Uses, Certifications, and Standards

| | |
|----------|----------|
| standard | UL E9809 |
|----------|----------|