



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



14W47AM STR Blade IP67 Plug 15A 125V 5-15P Anti-Mic

Pass & Seymour/LeGrand

Catalog Number	14W47AM
Manufacturer	Pass & Seymour/LeGrand
Description	Steriguard Anti-Microbial Wiring Devices Provide Excellent Protection Against The Growth Of Microbes On All Surfaces. Independent Testing Proves The Ability Of These Devices to Inhibit The Growth Of Escherichia Coli, Gram (-) and Staphylococcus Aureus, Gram (+) Providing Long Lasting Benefits to Manufacturers Beyond Conventional Cleaning Methods. Rated Watertight For 1, 500 Psi High-Pressure
Weight per unit	0.3500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Cable
Cord Type	S, SO, ST, SJ, SJO, SJT, 18/3, to 12/3, .300" min to .625" max diameter
Material	Thermoplastic
media	Yes
Number of Wires	3
Phase	1
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wire Size	18-12

Material, Color, and Finish

Color	Yellow
-------	--------

Dimensions and Weight

Depth	2.68
Width	1.63



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	STR BLADE IP67 PLUG 15A 125V 5-15P ANTI-MIC
extra long description	P&S 14W47AM STR BL IP67 PLUG 15A 12
Long Description	SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure
Product Type	STR BL IP67 Plug 15A 125V 5-15P Anti-Mic
Special Features	Watertight

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007056976
Manufacturers Part Number	14W47AM
UPC	785007056976

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	IP67 Plug

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized
nema rating	4X/6P
standard	UL, CSA, CSA Listed, FSUL, UL Listed