




Atlanta, Georgia

Phone 800-521-7326

Fax 770-745-1333

Turned Eye Bolt With Hex Nut Zinc Plated



Diameter D	Thread Length F	Overall Length S	Shank Length T	Inside Eye Size C	Thread Diameter W	Thread Diameter F	Wire Pieces Per Jar	Pieces Per Case	Lbs. Per 100 Pcs.	Maximum Work Load In LBS
3/16	1-3/4	1	7/8	3/8	10-24	.160	N/A	200	2.2	50
3/16	2-1/4	1-1/2	1-3/8	3/8	10-24	.160	N/A	200	2.4	50
3/16	2-1/2	1-3/4	1-5/8	3/8	10-24	.160	100	500	2.7	50
3/16	2-3/4	2	1-7/8	3/8	10-24	.160	N/A	200	2.9	50
3/16	3	2-1/4	2-1/8	3/8	10-24	.160	100	500	3.2	50
1/4	2	1	7/8	9/16	1/4-20	.214	100	600	4.6	75
1/4	2-1/2	1-1/2	1-3/8	9/16	1/4-20	.214	100	600	5.1	75
1/4	3	2	1-3/4	9/16	1/4-20	.214	50	300	5.8	75
1/4	4	3	2-3/4	9/16	1/4-20	.214	50	300	6.8	75
1/4	5	4	3	9/16	1/4-20	.214	50	300	7.5	75
1/4	6	5	3	9/16	1/4-20	.214	50	300	8.9	75
1/4	8	7	3	9/16	1/4-20	.214	N/A	200	11.5	75
5/16	2-1/4	3/4	1/2	3/4	5/16-18	.272	N/A	200	7.7	100
5/16	3-1/4	1-3/4	1-1/2	3/4	5/16-18	.272	50	300	10.3	100
5/16	4	2-1/2	2-1/4	3/4	5/16-18	.272	50	300	12	100
5/16	5	3-1/2	3	3/4	5/16-18	.272	50	300	14	100
5/16	6	4-1/2	3	3/4	5/16-18	.272	50	300	14.8	100
5/16	8	6-1/2	3	3/4	5/16-18	.272	N/A	200	18.7	100
3/8	2-1/2	3/4	1/2	1	3/8-16	.331	N/A	200	14.5	125
3/8	4	2-1/4	2	1	3/8-16	.331	25	150	18.4	125
3/8	5	3-1/4	3	1	3/8-16	.331	20	120	21.1	125
3/8	6	4-1/4	3	1	3/8-16	.331	50	300	23.9	125
3/8	8	6-1/4	3-7/8	1	3/8-16	.331	50	300	28	125
7/16	8	6	3	1-1/8	7/16-14	.380	N/A	200	40	125
1/2	4	1-3/4	1-1/4	1-1/4	1/2-13	.445	25	150	36.1	250
1/2	6	3-3/7	3	1-1/4	1/2-13	.445	25	150	44.9	250
1/2	8	5-3/4	3-7/8	1-1/4	1/2-13	.445	25	150	55	250
1/2	10	7-3/4	3-7/8	1-1/4	1/2-13	.445	25	150	62.9	250
1/2	12	9-3/4	3-7/8	1-1/4	1/2-13	.445	N/A	200	71.3	250

Material: Zinc Chromate Finish

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.