



1-Gang



2-Gang



2-Gang,
Toggle &
Duplex
Receptacle



1-Gang,
0.375" Hole



GFER



2160



231



153

Blank - Box Mounted

Description	Material	Catalog No.	Colors	
1-Gang	Thermoset	□ 2729__	V, W	•
	302/304 Stainless Steel	□ 93851	—	•
2-Gang	302/304 Stainless Steel	□ 93852	—	•

Combination 2-Gang

Description	Material	Catalog No.	Colors	
Toggle & Duplex Receptacle	Thermoset	□ 2148__	B, V, W	•

Telephone & Coax

Description	Material	Catalog No.	Colors	
1-Gang with 0.37" (9.5mm) Hole	Thermoset	□ 2728__	V, W	•
	302/304 Stainless Steel	□ 93896	—	•

Wallplate Accessories

Description	Finish/Material	Catalog No.	Colors	
GFCI Extension Ring for use with GFCIs, 7/8" spacer	—	□ GFER-__**	B, BK, LA, V, W	
Adapter - Decorator to Blank	—	□ 2160__	B, V, LA, W	•
Adapter - Decorator to Toggle	—	□ 2161__	V, W	•
Toggle & Receptacle Wallplate Screws #6-32 x 1/2" (12.7mm) for Toggle & Receptacle Wallplates	Baked Enamel Head/Metal	□ 231__	A, B, V, LA, W	
	Nylon	□ 232__	RD, V, W	
Toggle & Receptacle Wallplate Screws #6-32 x 5/16" (7.9mm) for Toggle & Receptacle Wallplates	Baked Enamel Head/Metal	□ 2231__	V, LA, W	
Recessed Pilot Light Lamp Holder with 6 Watt Clear S-6 Bulb	—	□ 153*†	—	•

*For use with louver wallplate

** cULus certified

† UL, CSA certified

Color Ordering Information

For ordering wallplates, include Cat. No. followed by the color code: A (Almond), B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Light Almond), RD (Red), RN (Orange), V (Ivory), W (White)

Icon Key

NAFTA Compliant - see page O-30

Certifications

2000 series wallplates are cULus certified
90000 series wallplates are UL and CSA certified

Specification Information:

Wallplates: J-21