

Eaton 1547

Catalog Number: 1547

Eaton Arrow Hart severe duty straight blade connector, #14-8 AWG, 15A, Industrial, 125V, Back wire, Yellow, black, Nickel-plated brass, Corrosion Resistant, Nylon, 5-15R, Two pole, three wire, grounding, Screw, 0.38-1" in diameter, Thermoplastic, Core pack

General specifications

Product Name	Catalog Number
Eaton Arrow Hart severe duty straight blade connector	1547
	UPC
	040893630809
Product Length/Depth	Product Height
1.69 in	2.78 in
Product Width	Product Weight
1.69 in	0.24 lb
Warranty	Certifications
Refer to warranty document.	cULus Listed



Product specifications

Device type

Connector

Color

Yellow

Black

Face/body material

Nylon

Wiring method

Back wire

Material

Thermoplastic

Allowable wire size

#14-8 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Nickel plated brass

Type

Complex environment

Device grade

Severe duty

NEMA configuration

5-15R

Style type

Straight body

Environmental conditions

Corrosive

Design type

Straight blade

Environmental resistance

Corrosion resistant

Connection type

Screw

Resources

Brochures

[Complex environment devices brochure](#)

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 1547](#)

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Cord range

0.38-1" in diameter

Voltage rating

125V

Application

Industrial

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)