



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1597TRWRI Radiant Self Test TR WR GFCI 15A 125V Iv *Pass & Seymour/Legrand*

Catalog Number	1597TRWRI
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test Duplex Receptacle, 15 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Ivory, 0.025 Sec Trip Time, Weather Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	15
connection	Back and side wire
indoor/outdoor	Outdoor
interrupt rating	4 to 6 mA
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Tamper-Resistant, Self-Test, Weather-Resistant, GFCI
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Length	1.03
Width	1.73

Descriptions

Description	RADIANT SELF TEST TR WR GFCI 15A 125V IV
extra long description	P&S 1597TRWRI RADIANT SELF TEST TR

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007036138
UPC	785007036138

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Specification Grade Weather-Resistant 15A Self-Test Duplex GFCI

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	CULUS, UL, cULus, UL Listed, FSUL