



A15

SPECIALTY INCANDESCENT LAMPS

Incandescent A15 Lamps for Utility, Fan, Appliance and Garage Lighting Applications

DOUBLElife™ Incandescent A15 Lamps

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
40	3.50	Medium	11664	40A15/DL/SW/BL/2/24 120V	120	24	Soft White	2000	2850	100	310	C-9	●●
			10034	40A15/CL/DL/FAN/2/12/BL 120V	120	12	Clear	2000	2850	100	350	C-9	●● ¹³
			10133	40A15/DL/CL/APPL/BL 120V	120	12	Clear	2000	2850	100	350	C-9	●●
			10061	40A15/CL/DL/APPL/2/12/BL 120V	120	12	Clear	2000	2850	100	350	C-9	●●
60	3.50	Medium	10868	60A15/DL/SW/BL/2/24 120V	120	24	Soft White	2000	2850	100	510	C-9	●●
			10040	60A15/CL/DL/FAN/2/12/BL 120V	120	12	Clear	2000	2850	100	530	C-9	●● ¹³
			10048	60A15/CL/DL/FAN/RP 120V	120	24	Clear	2000	2850	100	530	C-9	●● ¹³

Standard Incandescent A15 Lamps

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
15	3.50	Medium	10018	15A15/CL 120V	120	120	Clear	2500	2850	100	105	C-9	●●
			10019	15A15/CL 130V	130	120	Clear	2500	2850	100	105	C-9	●●
			10031	15A15/RP 120V	120	24	Inside Frost	2500	2850	100	100	C-9	●●
			10037	15A15 120V	120	120	Inside Frost	2500	2850	100	100	C-9	●●
			10038	15A15 130V	130	120	Inside Frost	2500	2850	100	100	C-9	●●
			10015	15A15/W/RP 120V	120	24	Soft White	2500	2850	100	65	C-9	●●
30	3.50	Medium Brass	10122	30A15 130V	130	120	Inside Frost	2000	2850	100	200	C-9	●
40	3.50	Medium	10042	40A15/CL/FAN 120V	120	24	Clear	1000	2850	100	430	C-9	●● ¹³
			10036	40A15/CL/FAN/2/12/BL 120V	120	12	Clear	1000	2850	100	430	C-9	●● ¹³
			10141	40A15/2PK/RP 120V	120	24	Clear	1000	2850	100	430	C-9	●●
			10181	40A15/DAY/FAN/BL/2/24 120V	120	24	Daylight	1000	2850	100	340	C-9	●● ¹³
			10082	40A15/SL 120V	120	120	Inside Frost	1000	2850	100	410	C-9	●●
			10117	40A15/IF/BL 120V	120	12	Inside Frost	1000	2850	100	410	C-9	●●
			10119	40A15 120V	120	120	Inside Frost	1000	2850	100	410	C-9	●●
			11533	40A15/SWFAN/2/12/BL 120V	120	12	Soft White	1000	2850	100	405	C-9	●● ¹³
40	3.38	Candelabra	11534	40A15C/SW/FAN/2/12/BL 120V	120	12	Soft White	1000	2850	100	350	C-9	●● ¹³
			10029	40A15C/CL/FAN/2/12/BL 120V	120	12	Clear	1000	2850	100	375	C-9	●● ¹³
40	3.50	Medium	10066	40A15/CL/APPL/2/12/BL 120V	120	12	Clear	1000	2850	100	430	C-9	●●
			10129	40A15/CL/APPL/BL 120V	120	12	Clear	1000	2850	100	430	C-9	●●
60	3.50	Medium	10884	60A15CL/FAN/2/12/BL 120V	120	12	Clear	1000	2850	100	700	C-9	●● ¹³
60	3.38	Candelabra	10894	60A15C/CL/FAN/2/12/BL 120V	120	12	Clear	1000	2850	100	650	C-9	●● ¹³
60	3.50	Medium	10162	60A15/DAY/FAN/BL/2/24 120V	120	24	Daylight	1000	2850	100	560	C-9	●● ¹³
			10885	60A15/SWFAN/2/12/BL 120V	120	12	Soft White	1000	2850	100	680	C-9	●● ¹³
60	3.38	Candelabra	10777	60A15C/SW/FAN/2/12/BL 120V	120	12	Soft White	1000	2850	100	625	C-9	●● ¹³
60	3.50	Medium Brass	10886	60A15/GARAGE/2/12/BL 120V	120	12	Inside Frost	1000	2850	100	700	C-9	●

Specifications subject to change without notice.

Notes on page 53