



**Product Number:** 18038

**Order Abbreviation:** 15T6 130V

**General Description:** Incandescent T6 Bulb Shape Clear Finish Candelabra Base 15Watt 130Volt

#### Product Information

Abbrev. With Packaging Info.	15T6 130V 60/CS 10/SKU
Approx. Lumens	105
Average Rated Life (hr)	2000
Base	Candelabra
Bulb	T6
Class	B (vacuum)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	0.750
Diameter (mm)	19.05
Filament	C-7A
Lamp Finish	Clear
Maximum Overall Length - MOL (in)	3.063
Maximum Overall Length - MOL (mm)	77.7875
Nominal Voltage (V)	130.00
Nominal Wattage (W)	15.00

