

Eaton 1723-BOX

Catalog Number: 1723-BOX

Eaton straight blade plug , #18-10 AWG, 15A, Commercial, 125V, Back wire, Black, Brass, Thermoplastic, 1-15P, Two-pole, two-wire, non grounding, Screw, Thermoplastic rubber, ED Box



General specifications

Product Name	Catalog Number
Eaton straight blade plug	1723-BOX
UPC	Product Length/Depth
032664480607	2.75 in
Product Height	Product Width
1.5 in	1.5 in
Product Weight	Warranty
0.115 lb	Refer to warranty document.

Certifications

UL

NOM

Federal Specification Classification 6221

02



Powering Business Worldwide

Product specifications

Special features

- Non-grounding
- Non-polarized

Device type

Plug

Color

Black

Face/body material

Thermoplastic

Wiring method

Back wire

Features

- Non-grounding
- Non-polarized

Material

Thermoplastic rubber

Allowable wire size

#18-10 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Rubber plug

Device grade

Commercial

NEMA configuration

1-15P

Style type

Straight body

Design type

Straight blade

Connection type

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Commercial and residential straight blade vinyl receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 1723-BOX](#)

Screw

Number of wires

2

Receptacle type

Two-pole, two-wire, non grounding

Voltage rating

125V

Application

Commercial

Torque rating

14 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)