

# Eaton 1MCB400R

Catalog Number: 1MCB400R

Eaton main circuit breaker, 400A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, KD, Three-wire, Single-phase, 120/240V, (2) #3/0 AWG-250 kcmil, (1) #2/0 AWG-500 kcmil



## General specifications

### Product Name

Eaton main circuit breaker

### Catalog Number

1MCB400R

### UPC

786849053192

### Product Length/Depth

15 in

### Product Height

15 in

### Product Width

24 in

### Product Weight

106 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil]. Add CL to end of catalog number for compression lug pads (includes lug pads for lines and neutral).

## Product specifications

### Amperage Rating

400 A

### Bus material

Aluminum

### Feed type

Top/bottom

### Phase

Single-phase

### Voltage rating

120/240 V

### Utility approvals

MI : DTE Energy (Detroit Edison)

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

NC : Dominion

VA : Dominion

### Enclosure

NEMA 3R

### Interrupt rating

65 kAIC

### Main circuit breaker

KD

### Number of wires

3

### Wire size

(2) #3/0 AWG-250 kcmil

(1) #2/0 AWG-500 kcmil

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - 1MCB400R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)