



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2008B 480V 1000W Turnlock

Nsi Industries

| | |
|------------------|-----------------------------------|
| Catalog Number | 2008B |
| Manufacturer | Nsi Industries |
| Description | Turnlock Relay Electronic 480V Ir |
| Weight per unit | 0.2100 (lbs/each) |
| Product Category | Electronic Time Switches |

Features

| | |
|----------------|-------------|
| supply voltage | 400-550 VAC |
| Timing Range | Instant On |

Dimensions and Weight

| | |
|------|-------------------|
| Size | H=2.187 - W=3.187 |
|------|-------------------|

Descriptions

| | |
|------------------------|--|
| Description | 480V 1000W TURNLOCK |
| extra long description | TORK 2008B 36 Crct Stacked Neutral |
| Features | Electronic Instant Response TurnLock, On 1.3-1.7, Off/On Ratio 1.5:1, 400-550V, 1000W Tungsten, 1800VA Ballast, 4A LED |
| Long Description | TurnLock Relay Electronic 480V IR |
| Product Type | 36 CRCT Stacked Neutral |
| Special Features | 360 Joule MOV (Metal Oxide Varistor) Surge Arrestor - Instant On - 3-5 Seconds Off |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00786261620170 |
| Manufacturers Part Number | 2008B |
| UPC | 786261620170 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Commercial dimmers, motion sensors, & photo cells |
| Type | Instant Response Turn Lock Photocontrol |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.21 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|-------------------------|
| Application | Street-Highway Lighting |
| Enclosure | Polycarbonate |
| environmental conditions | -40 to + 158 F |
| Frequency Rating | 50-60 Hz |
| Mounting | TURN LOCK |
| Operating Temperature | -40 to + 158 F |