


## High Tension Hand Hacksaw Frames & Blades

### 5012 LOW PROFILE FRAME

#### Specifications

Product Number	Description
20920-5012	Low profile, high tension hand hacksaw frame



#### THE LENOX® ADVANTAGE™

- **Fits into tight spots**  
Low profile tip easily handles close-quarter cuts.
- **Fast, straight cuts**  
Tensions up to 28,000 PSI.

### 4012 HIGH TENSION FRAME

#### Specifications

Product Number	Description
20918-4012	High tension hand hacksaw frame




#### THE LENOX® ADVANTAGE™

- **Comfortable grip**  
Ergonomic design and larger space fit gloved hands.
- **Convenient storage**  
Handle holds up to five 12" hacksaw blades for quick changeouts.
- **Multi-purpose**  
Mount at 45° for flush cutting; insert standard recip blade to use as a jab saw.
- **Fast, straight cuts**  
Tensions up to 30,000 PSI.

### 2012 LIGHTWEIGHT, ALL METAL FRAME

#### Specifications

Product Number	Description
20919-2012	Heavy-duty aluminum handle hacksaw frame with 12" bi-metal blade



#### THE LENOX® ADVANTAGE™

- **Great value**  
Affordable frame offers highest blade tension in its class.
- **Easy adjusting**  
Uses wing nut to adjust tension quickly.

## Bi-metal Hacksaw Blades

### Blade Specifications

Product Number Bulk Packed- 100 Per Pack	Product Number 10 Per Pack	Product Number Blister Packed- 1 Per Card/ 10 Cards Per Pack	TPI	Length x Width (Inches)
20110-018HE	20140-V018HE	20150-S018HE	18	10 x 1/2
20111-024HE	20141-V024HE	20151-S024HE	24	10 x 1/2
20112-032HE	20142-V032HE	20152-S032HE	32	10 x 1/2
	20143-V214HE		14	12 x 1/2
20116-218HE	20144-V218HE	20154-S218HE	18	12 x 1/2
20117-224HE	20145-V224HE	20155-S224HE	24	12 x 1/2
20118-232HE	20146-V232HE	20156-S232HE	32	12 x 1/2

#### THE LENOX® ADVANTAGE™

- **Shatter resistant**  
Bi-metal construction allows blades to bend and flex.
- **Longer life**  
*TUFF TOOTH™* design eliminates tooth strippage.




## High Tension Hand Hacksaw Frames & Blades

### 5012 LOW PROFILE FRAME

#### Specifications

Product Number	Description
20920-5012	Low profile, high tension hand hacksaw frame



#### THE LENOX® ADVANTAGE™

- **Fits into tight spots**  
Low profile tip easily handles close-quarter cuts.
- **Fast, straight cuts**  
Tensions up to 28,000 PSI.

### 4012 HIGH TENSION FRAME

#### Specifications

Product Number	Description
20918-4012	High tension hand hacksaw frame




#### THE LENOX® ADVANTAGE™

- **Comfortable grip**  
Ergonomic design and larger space fit gloved hands.
- **Convenient storage**  
Handle holds up to five 12" hacksaw blades for quick changeouts.
- **Multi-purpose**  
Mount at 45° for flush cutting; insert standard recip blade to use as a jab saw.
- **Fast, straight cuts**  
Tensions up to 30,000 PSI.

### 2012 LIGHTWEIGHT, ALL METAL FRAME

#### Specifications

Product Number	Description
20919-2012	Heavy-duty aluminum handle hacksaw frame with 12" bi-metal blade



#### THE LENOX® ADVANTAGE™

- **Great value**  
Affordable frame offers highest blade tension in its class.
- **Easy adjusting**  
Uses wing nut to adjust tension quickly.

## Bi-metal Hacksaw Blades

### Blade Specifications

Product Number Bulk Packed- 100 Per Pack	Product Number 10 Per Pack	Product Number Blister Packed- 1 Per Card/ 10 Cards Per Pack	TPI	Length x Width (Inches)
20110-018HE	20140-V018HE	20150-S018HE	18	10 x 1/2
20111-024HE	20141-V024HE	20151-S024HE	24	10 x 1/2
20112-032HE	20142-V032HE	20152-S032HE	32	10 x 1/2
	20143-V214HE		14	12 x 1/2
20116-218HE	20144-V218HE	20154-S218HE	18	12 x 1/2
20117-224HE	20145-V224HE	20155-S224HE	24	12 x 1/2
20118-232HE	20146-V232HE	20156-S232HE	32	12 x 1/2

#### THE LENOX® ADVANTAGE™

- **Shatter resistant**  
Bi-metal construction allows blades to bend and flex.
- **Longer life**  
*TUFF TOOTH™* design eliminates tooth strippage.

