



Powering Business Worldwide

### 2032A-BOX

Wallplate 1G Dup Recp Thermoset Mid AL

UPC: 032664542480

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Socket Extension

Special Features: Wattage 660 W, Extends 1.38 In, Size 1.50 In Diameter X 2.36 In Height

Application: Socket Extension

Standard: UL

Voltage Rating: 250 Vac

Amperage Rating: 660 Watts

Base: Medium

Connection: Push

Material: Phenolic

Color: Black

Mounting: Screw With Porcelain Base

### 2032B-BOX

Wallplate 1G Dup Recp Thermoset Mid BR

UPC: 032664150500

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Trouble Lamp Handle With Interior

Special Features: With (2) NEMA 1-15 2 Pole 2 Wire Outlet

Application: Replacement Trouble Lamp Handle

Standard: UL

Voltage Rating: 125 Vac

Amperage Rating: 6 Amp

Base: Medium

Connection: Push

Color: Yellow

Mounting: Screw

### 2032LA-BOX

Wallplate 1G Dup Recp Thermoset Mid LA

UPC: 032664582455

Brand Name: Eaton

Sub Brand: ARROW HART

Type: 1 Gang

Voltage Rating: 125 Vac

Amperage Rating: 15 Amp

Body: Cast Aluminum

Mounting: Surface/Wall



Powering Business Worldwide

### 2032V

Wallplate 1G Dup Recp Thermoset Mid IV

UPC: 032664314001

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: 1 Gang

Number Of Outlet: 4

Material: Cast Aluminum

Construction: Weatherproof

Cable Entry: (1) Back, (2) One End, (1) Other End

Mounting: Surface/Wall

Knockouts: Yes

### 2032W

Wallplate 1G Dup Recp Thermoset Mid WH

UPC: 032664443206

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: 1 Gang

Number Of Outlet: 5

Material: Cast Aluminum

Construction: Weatherproof

Cable Entry: (1) Back, (2) Each End

Mounting: Surface/Wall

Knockouts: Yes



Powering Business Worldwide

### 2032A-BOX

Wallplate 1G Dup Recp Thermoset Mid AL

UPC: 032664542480

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Socket Extension

Special Features: Wattage 660 W, Extends 1.38 In, Size 1.50 In Diameter X 2.36 In Height

Application: Socket Extension

Standard: UL

Voltage Rating: 250 Vac

Amperage Rating: 660 Watts

Base: Medium

Connection: Push

Material: Phenolic

Color: Black

Mounting: Screw With Porcelain Base

### 2032B-BOX

Wallplate 1G Dup Recp Thermoset Mid BR

UPC: 032664150500

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Trouble Lamp Handle With Interior

Special Features: With (2) NEMA 1-15 2 Pole 2 Wire Outlet

Application: Replacement Trouble Lamp Handle

Standard: UL

Voltage Rating: 125 Vac

Amperage Rating: 6 Amp

Base: Medium

Connection: Push

Color: Yellow

Mounting: Screw

### 2032LA-BOX

Wallplate 1G Dup Recp Thermoset Mid LA

UPC: 032664582455

Brand Name: Eaton

Sub Brand: ARROW HART

Type: 1 Gang

Voltage Rating: 125 Vac

Amperage Rating: 15 Amp

Body: Cast Aluminum

Mounting: Surface/Wall



Powering Business Worldwide

### 2032V

Wallplate 1G Dup Recp Thermoset Mid IV

UPC: 032664314001

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: 1 Gang

Number Of Outlet: 4

Material: Cast Aluminum

Construction: Weatherproof

Cable Entry: (1) Back, (2) One End, (1) Other End

Mounting: Surface/Wall

Knockouts: Yes

### 2032W

Wallplate 1G Dup Recp Thermoset Mid WH

UPC: 032664443206

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: 1 Gang

Number Of Outlet: 5

Material: Cast Aluminum

Construction: Weatherproof

Cable Entry: (1) Back, (2) Each End

Mounting: Surface/Wall

Knockouts: Yes