

### BI-METAL RECIPROCATING SAW BLADES

Long Lasting, Fast Cutting and Versatile

**LONG LIFE**

Patented tooth design provides long blade life

















**EFFICIENT CUTTING**

Optimized for specific applications

**DURABLE CONSTRUCTION**

Shatter resistant, bi-metal design provides the flexibility and durability single-metal blades can't



TPI	LENGTH x WIDTH x THICKNESS		1-PACK	5-PACK	25-PACK	50-PACK	APPLICATION	
	IN	MM	PROD NO	PROD NO	PROD NO	PROD NO		
4	6 x 3/4	x .050 152 x 19 x 1.3	20574S634R	20575634R	—	—		
6	4 x 3/4	x .050 102 x 19 x 1.3	—	20449456RP	—	—		
6	6 x 3/4	x .050 152 x 19 x 1.3	20571S636RP	20570636RP	20497B636RP	—		
6	6 x 3/4	x .035 152 x 19 x .9	20559S606R	20560606R	20492B606R	—		
6	6 x 7/16	x .050 152 x 11 x 1.3	20557S676RC	20556676RC	—	—		
6	6 x 3/4	x .050 152 x 19 x 1.3	20573S656R	20572656R	20530B656R	227500SB656R		
6	9 x 3/4	x .050 229 x 19 x 1.3	20587S956R	20582956R	20558B956R	227520SB956R		
6	12 x 3/4	x .050 305 x 19 x 1.3	20586S156R	20585156R	20495B156R	227550SB156R		
10	6 x 3/4	x .035 152 x 19 x .9	20561S610R	20562610R	20493B610R	227610SB610R		
10	8 x 3/4	x .050 203 x 19 x 1.3	20581S810R	20580810R	20590B810R	227530SB810R		
10/14	6 x 3/4	x .050 152 x 19 x 1.3	20592650R*	20374650R5	20515B650R			•
10/14	8 x 3/4	x .050 203 x 19 x 1.3	—	20577850R	20535B850R			•
10/14	12 x 3/4	x .050 305 x 19 x 1.3	20584S110R	20583110R	20491B110R	227580SB110R		•
10/14	6 x 3/4	x .035 152 x 19 x .9	—	12129635R	—	—		•
10/14	8 x 3/4	x .035 203 x 19 x .9	—	12130835R	—	—		•

\* This item is a 2-pack



Two 10/14 TPI General Purpose reciprocating blades featuring T2 Technology. The 0.035" thick blades are ideal for cutting wood, metal and plastic 12129635R, 12130835R



**LENOX T2™ TECHNOLOGY RECIPROCATING SAW BLADES**

A revolutionary new blade design that delivers up to 100% longer blade life and 25% faster performance in metal cutting applications versus the prior generation of LENOX reciprocating saw blades.

### BI-METAL RECIPROCATING SAW BLADES

Long Lasting, Fast Cutting and Versatile

**LONG LIFE**

Patented tooth design provides long blade life

















**EFFICIENT CUTTING**

Optimized for specific applications

**DURABLE CONSTRUCTION**

Shatter resistant, bi-metal design provides the flexibility and durability single-metal blades can't



TPI	LENGTH x WIDTH x THICKNESS		1-PACK	5-PACK	25-PACK	50-PACK	APPLICATION		
	IN	MM	PROD NO	PROD NO	PROD NO	PROD NO			
4	6 x 3/4	x .050	152 x 19 x 1.3	20574S634R	20575634R	—	—		
6	4 x 3/4	x .050	102 x 19 x 1.3	—	20449456RP	—	—		
6	6 x 3/4	x .050	152 x 19 x 1.3	20571S636RP	20570636RP	20497B636RP	—		
6	6 x 3/4	x .035	152 x 19 x .9	20559S606R	20560606R	20492B606R	—		
6	6 x 7/16	x .050	152 x 11 x 1.3	20557S676RC	20556676RC	—	—		
6	6 x 3/4	x .050	152 x 19 x 1.3	20573S656R	20572656R	20530B656R	227500SB656R		
6	9 x 3/4	x .050	229 x 19 x 1.3	20587S956R	20582956R	20558B956R	227520SB956R		
6	12 x 3/4	x .050	305 x 19 x 1.3	20586S156R	20585156R	20495B156R	227550SB156R		
10	6 x 3/4	x .035	152 x 19 x .9	20561S610R	20562610R	20493B610R	227610SB610R		
10	8 x 3/4	x .050	203 x 19 x 1.3	20581S810R	20580810R	20590B810R	227530SB810R		
10/14	6 x 3/4	x .050	152 x 19 x 1.3	20592650R*	20374650R5	20515B650R	—		•
10/14	8 x 3/4	x .050	203 x 19 x 1.3	—	20577850R	20535B850R	—		•
10/14	12 x 3/4	x .050	305 x 19 x 1.3	20584S110R	20583110R	20491B110R	227580SB110R		•
10/14	6 x 3/4	x .035	152 x 19 x .9	—	12129635R	—	—		•
10/14	8 x 3/4	x .035	203 x 19 x .9	—	12130835R	—	—		•

\* This item is a 2-pack



Two 10/14 TPI General Purpose reciprocating blades featuring T2 Technology. The 0.035" thick blades are ideal for cutting wood, metal and plastic 12129635R, 12130835R



**LENOX T2™ TECHNOLOGY RECIPROCATING SAW BLADES**

A revolutionary new blade design that delivers up to 100% longer blade life and 25% faster performance in metal cutting applications versus the prior generation of LENOX reciprocating saw blades.