



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2097HGRED Self Test Gfci Hosp GRD Recp 20A 12 RD

*Pass & Seymour/Legrand*

Catalog Number	2097HGRED
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Red, 0.025 Sec Trip Time, Impact Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
indoor/outdoor	Indoor
interrupt rating	4 to 6 mA
media	Yes
Outlet Type	GFCI, Indoor, Commercial, Self-Test
Poles	Double Pole
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage	125.0 V
Voltage Rating	125

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Length	1.03
Width	1.73

### Descriptions

Description	SELF TEST GFCI HOSP GRD RECP 20A 12 RD
extra long description	P&S 2097HGRED SELF-TEST GFCI HOS GR

### Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007035971
UPC	785007035971

### Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 20.0

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.275

## Uses, Certifications, and Standards

environmental conditions ..... 95% Humidity, UL 94 V2

Operating Temperature ..... -35°C to +66°C

standard ..... cULus