



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097TRWRGRY Radiant Self Test TR WR GFI 20A 125V Gy

Pass & Seymour/Legrand

Catalog Number	2097TRWRGRY
Manufacturer	Pass & Seymour/Legrand
Description	20A 125V Self-Test Tamper-Resistant Weather-Resistant Gfci Gray
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
interrupt rating	4 to 6 mA
Material	Thermoplastic
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73

Descriptions

Description	RADIANT SELF TEST TR WR GFI 20A 125V GY
extra long description	P&S 2097TRWRGRY RADIANT SLF TST TR
Long Description	20A 125V Self-Test Tamper-Resistant Weather-Resistant GFCI Gray
Product Type	Radiant SLF TST TR WR GFI 20A 125V Gry
Special Features	Pass & Seymour invented the GFCI receptacle, and at Legrand, we're constantly reinventing it to ensure the highest level of safety possible. From the most advanced self-testing device to audible alarms to nightlight combos, we're continuously resetting the bar on GFCI innovation and safety.

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007036312
Manufacturers Part Number	2097TRWRGRY
UPC	785007036312



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Specification Grade Weather-Resistant 20A Self-Test Duplex GFCI

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL