



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2097TRWRW Radiant Self Test TR WR GFI 20A 125V WH

*Pass & Seymour/Legrand*

Catalog Number	2097TRWRW
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, White, 0.025 Sec Trip Time, Weather Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
indoor/outdoor	Outdoor
interrupt rating	4 to 6 mA
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Weather-Resistant, Self-Test, Tamper-Resistant, GFCI
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Length	1.03
Width	1.73

### Descriptions

Description	RADIANT SELF TEST TR WR GFI 20A 125V WH
extra long description	P&S 2097TRWRW RADIANT SELF TEST TR

### Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007036107
UPC	785007036107

### Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 20.0

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.275

## Uses, Certifications, and Standards

environmental conditions ..... 95% Humidity, UL 94 V2

Operating Temperature ..... -35°C to +66°C

standard ..... UL, CULUS, cULus, UL Listed, FSUL