

Products

- > [Index](#)
- > [Featured Products](#)
- > [Cross Reference](#)
- > [UPC Search](#)

**Product Datasheet**

[Catalog Home](#) [Home Page](#)

[Search](#)

## 2150 -- EMT/Rigid/IMC Set Screw Coupling 2-1/2" Trade Size - Steel



**Product Specifications**

<b>Family</b>	Rigid and IMC Fittings & EMT Fittings
<b>Fittings Classification</b>	Steel - Set Screw Couplings
<b>Trade Size</b>	2-1/2"
<b>Standard Packaging</b>	Carton
<b>Ship Carton Length</b>	9.00
<b>Ship Carton Width</b>	7.25
<b>Ship Carton Height</b>	4.625
<b>WT. PER HU.</b>	144.0
<b>Unit Carton Quantity</b>	5
<b>Ship Carton Quantity</b>	5
<b>UPC Number</b>	050169021507
<b>Product UPC-A Labeled</b>	Yes
<b>Catalog PDF Page</b>	<a href="#">PDF Catalog Page</a>

**Applications**

- For use in dry locations to couple two ends of EMT conduit
- RACO® steel set screw couplings provide concrete-tight connections when taped
- RACO® set screw couplings are suitable for applications above 600V

**Product Features**

- All steel construction insures mechanical protection for the raceway
- Tri-head screws (1/2" to 2" trade sizes) may be installed using

- a slotted, Philips, or Robertson head screwdriver
- 2-1/2" to 4" trade sizes are also UL listed for use on Rigid/IMC conduit, allowing for design and installation flexibility
  - All components are zinc electroplated for corrosion protection

**Compliances**

C / UL / US