



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



231I 3/4" Ins Set/Screw Emt Connector *Bridgeport Fittings*

| | |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 231I |
| Manufacturer | Bridgeport Fittings |
| Description | Set Screw Emt Connector, 3/4 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, +105 °C Operating Temperature, 1-1/2 In Length, 1 In Diameter, 0.12 LB/Ea |
| Weight per unit | 0.1200 (lbs/each) |
| Product Category | Steel Insulated Straight Set S |

Features

| | |
|----------------|------------------|
| Connector Type | SET SCREW |
| insulation | Insulated Throat |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------------|
| Finish | Zinc Electroplated |
|--------|--------------------|

Dimensions and Weight

| | |
|------|-----|
| Size | 3/4 |
|------|-----|

Descriptions

| | |
|------------------------|-----------------------------------|
| Description | 3/4" INS SET/SCREW EMT CONNECTOR |
| extra long description | BPT 231-I 3/4 SS CONN. INS. STEEL |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747102317 |
| UPC | 781747102317 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | STEEL EMT FITTINGS |
| Type | CONNECTOR |

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Package | 250 |
| Weight Per each | 0.12 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------------------------------------------------------------------------------------------|
| Application | Used to secure steel EMT to box or enclosure. Concrete-tight when taped. Plastic insulator rated 105 degree C. |
| standard | cULus |