



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



234I 1-1/2" Ins Set/Screw Emt Connector *Bridgeport Fittings*

| | |
|------------------|--|
| Catalog Number | 234I |
| Manufacturer | Bridgeport Fittings |
| Description | Set Screw Emt Connector, 1-1/2 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, +105 °C Operating Temperature, 2-1/2 In Length, 2 In Diameter, 0.0080 LB/Ea |
| Weight per unit | 0.0080 (lbs/each) |
| Product Category | Steel Insulated Straight Set S |

Features

| | |
|----------------|------------------|
| Connector Type | SET SCREW |
| insulation | Insulated Throat |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------------|
| Finish | Zinc Electroplated |
|--------|--------------------|

Dimensions and Weight

| | |
|------|-------|
| Size | 1-1/2 |
|------|-------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 1-1/2" INS SET/SCREW EMT CONNECTOR |
| extra long description | BPT 234-I 1-1/2 SS CONN. INS. STEEL |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747102348 |
| UPC | 781747102348 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | STEEL EMT FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-------|
| Trade Size | 1-1/2 |
|------------|-------|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 60 |
| Weight Per each | 0.008 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Used to secure steel EMT to box or enclosure. Concrete-tight when taped. Plastic insulator rated 105 degree C.

standard

cULus