



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 24175 24175 24IN Natural Cable Tie

*Nsi Industries*

Catalog Number	24175
Manufacturer	Nsi Industries
Description	The Powergrp GRP-24175 50-Count Resealable Pack Of Type 21 Natural-Colored Super Heavy-Duty Cable Ties Are 24" Long, With 175LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 24" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .28" (7MM) and 7.36" (187MM) Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and S
Weight per unit	0.0300 (lbs/each)
Product Category	Tools & Testers

### Features

Warranty	1 YEAR
----------	--------

### Material, Color, and Finish

Finish	Natural
--------	---------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	24175 24IN NATURAL CABLE TIE
extra long description	NSI GRP-24175 PowerGRP Cable Tie Na
Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-24175 ties combine a self-locking design with an industrial strength 175lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-24175 ties are water
Long Description	The PowerGRP GRP-24175 50-Count Resealable Pack of Type 21 Natural-Colored Super Heavy-Duty Cable Ties are 24" long, with 175lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these cables ties around a wide range of equipment with a bundle diameter between .28" (7mm) and 7.36" (187mm) using the bent tips and serrated locking mechanism to form an effortless and s
Product Type	Powergrp Cable Tie Natural 24" 175LB (50PK)

## Manufacturer Information

Brand	NSi
GTIN	00662381009432
Manufacturers Part Number	GRP-24175
UPC	662381009432

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

## Availability

minimum qty	50
-------------	----

## Packaging

Carton	1
Package	50
Weight Per each	0.03

## Uses, Certifications, and Standards

standard	UL62275
Temperature Rating	-40F to 185F