

Eaton 24248 SC

Catalog Number: 24248 SC

Eaton B-Line series Type 1 junction boxes, 24" height, 8" length, 24" width, NEMA 1, Screw cover, SC enclosure, Surface mounted, Medium single door, 9 side knockouts, 9 top-bottom knockouts, Thru holes, Carbon steel

General specifications

Product Name	Catalog Number
Eaton B-Line series Type 1 junction boxes	24248 SC
	UPC
	782051233100
Product Length/Depth	Product Height
8 in	24 in
Product Width	Product Weight
24 in	43.1 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	



Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

SC enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

Thru holes

Special features

Keyhole slots on cover, plated screws

Top knockouts

9

Side knockouts

9

Bottom knockouts

9

Standards

NEMA Rating

1

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 24248 SC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)