



FITTINGS APPROVED FOR USE WITH ALUMINUM EMT

FITTING STYLE	UL File E24001
SETSCREW TYPE	230-DC2, -DCI2 thru 234-DC2, -DCI2
	235-DC, -DC2, -DCI, -DC2I
	236-DC, -DCI thru 239-DC, -DCI
	234-SBLK, -SR, -SO, -SY, -SG, -SBLU, -SW
	244-SBLK, -SR, -SO, -SY, -SG, -SBLU, -SW
	240-DC thru 249-DC
COMPRESSION TYPE	250-DC2, -RT2, -DCI2, -RTI2 thru 254-DC2, -RT2, -DCI2, -RTI2
	255-DC2, -DCI2 thru 259-DC2, -DCI2
	260-DC2, -RT2, -DCI2, -RTI2 thru 264-DC2, -RT2, -DCI2, -RTI2
	265-DC thru 269-DC
PUSH-EMT® TYPE	250-MSRT, 251-MSRT
	260-MSRT, 261-MSRT



FITTINGS APPROVED FOR USE WITH ALUMINUM EMT

FITTING STYLE	UL File E24001
SETSCREW TYPE	230-DC2, -DCI2 thru 234-DC2, -DCI2
	235-DC, -DC2, -DCI, -DC2I
	236-DC, -DCI thru 239-DC, -DCI
	234-SBLK, -SR, -SO, -SY, -SG, -SBLU, -SW
	244-SBLK, -SR, -SO, -SY, -SG, -SBLU, -SW
	240-DC thru 249-DC
COMPRESSION TYPE	250-DC2, -RT2, -DCI2, -RTI2 thru 254-DC2, -RT2, -DCI2, -RTI2
	255-DC2, -DCI2 thru 259-DC2, -DCI2
	260-DC2, -RT2, -DCI2, -RTI2 thru 264-DC2, -RT2, -DCI2, -RTI2
	265-DC thru 269-DC
PUSH-EMT® TYPE	250-MSRT, 251-MSRT
	260-MSRT, 261-MSRT